

Set de verificación de calibración Checker® HC color del agua

HI727-11



Descripción

El set de verificación de calibración del color del agua para Checker® HC **HI727-11** proporciona una solución simple para validar el Checker® HC para color del agua **HI727** que tiene un rango de 0 a 500 PCU. Este set de estándares de alta calidad se fabrica en nuestras instalaciones de última tecnología y viene con un certificado de análisis. El certificado de análisis proporciona el número de lote, los valores de referencia y la fecha de vencimiento para la trazabilidad al verificar el Checker® HC.

Especificaciones

| | |
|-------------------------|----|
| Certificado de análisis | Si |
|-------------------------|----|

| | |
|----------------------|---------|
| Envase | Cubetas |
| Cantidad de análisis | 1 juego |

Accesorios

No Especifica

Cómo pedir

No Especifica

Ventajas

El **HI727-11** es un set de estándares de calibración de alta calidad que permite a los usuarios validar el Checker® HC para color del agua **HI727**. El **HI727-11** incluye una cubeta sellada para cero PCU y una cubeta con coloración equivalente a 150 +/- 15 PCU a 25°C.

-Reutilizable con larga vida útil.

-Se suministra con certificado de análisis:

- Código de producto
- Número de lote
- Fecha de caducidad



CERTIFICATE OF ANALYSIS

Product Name: CALIBRATION CHECKING SET FOR HI 711
 Product Code: HI 711-11
 Lot number: SC0372/14
 Expiration date: October 2017

| Standard cuvette | Lot number | Standard Value @ 25°C (ppm) | Passed |
|------------------|------------|-----------------------------|--------|
| A, HI 711-11 | 2038 | 1.00 ± 0.05 | ✓ |
| B, HI 711-11 | 2039 | 1.00 ± 0.05 | ✓ |

Hanna Instruments certifies these standards meet the stated tolerance limits as indicated. These should be used for quality control to validate instrument function on the specified Hanna instrument only. Store standards in the storage box upright at room temperature. Do not use standard cuvettes.


Instructions for use:

1. Thoroughly wipe standard cuvette with HI731318 lint free cloth and only handle using top of cuvette. The cuvette wall must be dry and free of smudges.
2. At the C.1 prompt place A, HI 711-11 standard cuvette into the holder of the Checker and press operations button.
3. At the C.2 prompt place B, HI 711-11 standard cuvette into the holder and press the operations button.

Acceptable results must be between 0.95 and 1.05 ppm @ 25°C.

File number: CERT711-11_SC0372/14

QA manager: Bogdan Munteanu



Video

No Especifica